



Built for the harshest medical environments, P&S power indicating receptacles feature two industry-exclusive green LEDs that offer clear visual assurance of power indication at the receptacle even with critical equipment plugged into the device. The LEDs operate independently from one another to accommodate split-circuit wiring installations. Tamper-resistant protection comes standard with each receptacle to further enhance safety.

### Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Auto-ground clip assures positive ground.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	Backed-out tri-drive brass terminal screws for faster installation.
Internal screw-pressure-plate back and side wire capability.	Two back wire holes for additional wiring flexibility.
Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.	.032 inch thick brass triple-wipe power contacts.
Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .	Wire Size: #14 - #10 AWG Copper Conductor Only

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Application Sector	Hospital Grade
Standard	CSA Listed, UL Listed, FSUL		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Dielectric Strength	Withstands 2000V minimum	Phase	Single
---------------------	--------------------------	-------	--------

Connection	Side & Back Wired	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125 V	Environmental Conditions	UL94 V2