



Wattstopper
Wattstopper PLUS Ceiling Mount GreenBus Sensor/Photocell, 450 square feet
Part No. BCS_WA_EN-SCPPH-0450-GB2



The EN-SCPPH-0450-GB2 is a ceiling/surface mount sensor that combines both Passive Infrared (PIR) and Photocell sensing into a single device. With a range of 450 sq. ft., the GreenBus sensor connects to the Wattstopper PLUS system through a GreenBus cable with a standard 2-pin connector.

Features & Benefits

Occupancy Sensor & Photocell built into one device	Simple Installation, using magnetic mounting and 360 degree directional flexibility
Reposition sensor with no noticeable substrate marks	Customize time-out settings using the Wattstopper PLUS Software

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	840356700281	Country Of Origin	Canada
Features	Flame Retardant	Installation Location	Ceiling
Included	Decorator Strap, Mounting Screws, Sensor Mask	Application Sector	Commercial, Industrial
Warranty Type	5-Year	Type	Sensor

Dimensions

Product Width US	3.37 in	Product Weight US	0.5 lb
Product Height US	1.13 in	Product Length US	3.37 in

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

cUL Listed	Yes
------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Has Battery	Yes	Number of Connections	2
-------------	-----	-----------------------	---

Sensor Coverage Pattern	360 deg	Sensor Type	Daylight, Occupancy
-------------------------	---------	-------------	---------------------

Sensor Mounting Height	8-10 ft	Sensor Technology	Passive Infrared (PIR)
------------------------	---------	-------------------	------------------------

Topology	Daisy Chain	Indoor/Outdoor	Indoor
----------	-------------	----------------	--------

Sensor Coverage	450 sq ft	Mounting Type	Magnetic, Surface Mount
-----------------	-----------	---------------	-------------------------

On Function	Selectable Auto/Manual	Current Draw	3 mA
-------------	------------------------	--------------	------

Operating Temperature	32°-104°F	Operating Humidity	0-90% RH (Non-Condensing)
-----------------------	-----------	--------------------	---------------------------

Sensing Range	24 ft	Wire Connection Type	Flying Leads
---------------	-------	----------------------	--------------
