



Wattstopper DLM Low Voltage 1-Button Shade Wall Switch

Part No. BCS_WA_LMSH-SW101I



Legrand's series wall switches are low voltage device for manual control of shades in one or more locations. This device has 1 or more buttons and can control any shade motors connected to DLM shade controllers. The switches connect using standard DLM IRB RJ45 cables and have a counter balanced design that allows shades to be pulled into position from the hembar.

Features & Benefits

Available in four different switch configurations to support control of any shade project

Switches are pre-engraved with most common control configurations

Customizable buttons with LED status indicators

Includes system configuration button for easy system programming from the switch

Components of Digital Lighting Management integrated shade control system

Available in six color options: White, Black, Grey, Ivory, Light Almond and Red

Plug n' Go automatic configuration along with Pull n' Save and Push n' Learn for system personalization

Matches DLM Lighting Control switches for consistent design of lighting and shade control

IR transceiver for wireless configuration and remote control

Custom engraving or engraved and non-engraved button kits available

Specifications

General Info

Product Line	Wattstopper	Color	Ivory
UPC Number	842854000269	Country Of Origin	China
Product Series	LMSW-SH	Number of Switches	1
Application Sector	Commercial	Warranty Type	Lifetime
Type	Switch		

Dimensions

Product Width US	1.8 in	Product Weight US	0.15 lb
------------------	--------	-------------------	---------

Product Volume US	22.8 cu in	Product Depth US	1.6 in
-------------------	------------	------------------	--------

Product Height US	4.1 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

FCC Compliant	Yes	cUL Listed	Yes
---------------	-----	------------	-----

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

Technical Information

Operating Temperature Min	0 °C	Has Battery	No
---------------------------	------	-------------	----

Operating Temperature Max	55 °C	Number of Buttons	0
---------------------------	-------	-------------------	---

Number of Rockers	1	Input Voltage	24 VDC
-------------------	---	---------------	--------

Indoor/Outdoor	Indoor	Current Draw	5 mA
----------------	--------	--------------	------

Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	--------------------	--------------------	------------------------------

Wire Connection Type	RJ-45	Engraving Type	Icon
----------------------	-------	----------------	------
